

## Fest eingestelltes Druckreduzierventil für Wasser



### Pre-set regulator valve for water



#### Technische Daten

Max. Eingangsdruck:	10 bar
Ausgangsdruck:	Siehe Tabelle
Toleranz*:	1.0 bar – 3.0 bar: +/- 0.3 bar 3.5 bar – 7.0 bar: +/- 10%
Anschluss:	1/4" BSP IG – IG
Temperaturbereich:	4°C bis 60°C
Durchfluss:	Siehe Tabelle
Gehäuse:	Messing, vernickelt
Innenteile:	DIN 1.4404 / AISI 316L
Membrane:	NBR
Sitz:	PPH, Santoprene
Gewicht:	Ca. 125g

#### Auf Anfrage:

- Ausführung mit FPM Membrane
- Ausführung in Ecobrass

\*Prüfmedium: Luft, Pe = 6 bar (bei Pa ≤ 4 bar), 10NI/min  
Luft, Pe = 10 bar (bei Pa > 4 bar), 10NI/min



#### Technical data

Max. inlet pressure:	10 bar
Outlet pressure:	See table
Tolerance*:	1.0 bar – 3.0 bar: +/- 0.3 bar 3.5 bar – 7.0 bar: +/- 10%
Connection:	1/4" BSP female-female
Working temperature:	4°C to 60°C
Flow:	See table
Body:	Brass nickel plated
Inner parts:	DIN 1.4404 / AISI 316L
Diaphragm:	NBR
Seat:	PPH, Santoprene
Weight:	Ca. 125g

#### On request:

- Version with FPM diaphragm
- Version in Ecobrass

\*Test medium: air, Pe = 6 bar (at Pa ≤ 4 bar), 10NI/min  
air, Pe = 10 bar (at Pa > 4 bar), 10NI/min



TRI-IN-LINE FLUIDREG "WASSER" / "Water"		
No. TRI-MATIC	Code / Ausgangsdruck / Outlet pressure	**Durchfluss / Flow ml/min (Pe = 10 bar, Δp 0.8 bar)
1705424	239 A 0210 G1/4 IG/IG 1 BAR	10 000
1705425	239 A 0215 G1/4 IG/IG 1.5 BAR	10 000
1705147	239 A 0220 G1/4 IG/IG 2 BAR	10 000
1714785	239 A 0225 G1/4 IG/IG 2.5 BAR	10 000
1705428	239 A 0230 G1/4 IG/IG 3 BAR	10 000
1705429	239 A 0235 G1/4 IG/IG 3.5 BAR	10 000
1704777	239 A 0240 G1/4 IG/IG 4 BAR	10 000
1715179	239 A 0250 G1/4 IG/IG 5 BAR	10 000
1712975	239 A 0260 G1/4 IG/IG 6 BAR	10 000
1705475	239 A 0270 G1/4 IG/IG 7 BAR	10 000

\*\*Durchfluss für liquides Medium / Flow rate for liquid medium

Bitte fragen Sie unsere aktuellen Preise an!

Do not hesitate to contact us for current prices!

TRI-MATIC AG - CH-6331 Hünenberg  
TRI-MATIC SA - CH-1400 Yverdon-les-Bains

**tri-matic.ch**

Tel 041 780 22 22 info@tri-matic.ch  
Tel 024 426 12 13 filiale@tri-matic.ch